

PACLITE

The newest, strongest, and lightest, flatwire belt on the market

PacLite

- Dedicated sprocket openings reduce picket distortion
- Variable number of sprocket openings across width
- Standard, can duty and heavy duty available
- NokLok™ picket technology increases picket strength



Advantages

- Lasts 30% longer than competitors flatwire belts
- 10% lighter than traditional flatwire belts in the market
- Up to 20% more open area for superior fluid and air movement
- Significantly less stretch and distortion
- Excellent strength-to-weight ratio

BeltTechSpecs

- Widths up to 256" (6500mm)
- Speeds up to 250fpm (76mpm)
- Temperatures to 1000°F (538°C)
- Materials: T316LSS, WRSS, T304SS, HCS, GALV
- Available in Can Duty, Heavy Duty, and Standard Duty



PacLite: When strength and lightweight efficiency are what matters